

DIGITUS® Estrutura de mesa com regulação eléctrica em altura, 90° em L, motor triplo, 2 passos, cinzento

DA-90459

EAN 4016032502142



Estrutura de mesa regulável eletricamente em altura, em forma de L Altura: 120 cm, carga: 120 kg, cinzento

Com a estrutura de secretária eletricamente regulável em altura da DIGITUS®, pode facilmente transformar a sua secretária numa estação de trabalho ergonómica sit/stand. Poupe o tempo e o dinheiro de encontrar uma secretária com altura regulável e utilize o nosso kit de atualização com regulação eléctrica. Este modelo pode ser utilizado para tampos de mesa de 120-180 cm e 140-200 cm de comprimento. São recomendadas profundidades de tampo de mesa de 55 a 100 cm. Pode guardar 4 posições de altura através do painel de controlo e ajustá-las em qualquer altura com o toque de um botão. A altura atual é mostrada no visor LED. A proteção contra colisão integrada evita colisões com potenciais obstáculos quando a mesa é levantada ou baixada.

Transforme a sua secretária numa estação de trabalho ergonómica, em pé ou sentado. Regulável eletricamente em altura, extensível de forma variável e pode ser instalada à direita. Com proteção contra colisões e função de memória para a regulação em altura.

- Capacidade máxima de carga até 120 kg
- Estrutura ajustável de forma flexível: Travessa transversal (112 - 165 cm) x travessa longitudinal (130 - 180 cm)
- Adequado para tampos de mesa: 120 - 180 cm x 140 - 200 cm e uma profundidade de 55 - 100 cm

- A escora longitudinal (3ª perna) pode ser montada de forma flexível à direita
- Regulação confortável e eléctrica da altura (sem tampo da mesa): 72 - 120 cm
- Painel de controlo da regulação da altura com ecrã LED (3 níveis de luminosidade) e função de memória para 4 níveis de altura
- Função de proteção contra colisão (sensor G) com 3 níveis de sensibilidade - deteção de obstáculos durante o movimento para cima e para baixo
- Sistema de paragem automática - Pára o motor em caso de resistência e retrai automaticamente o quadro
- 3 motores para uma regulação em altura fácil e silenciosa (< 50 dB) - Velocidade de elevação 25 mm/seg.
- 3 pés (58,5 cm de largura), cada um com 2 pés de apoio para um ajuste fino para compensar pisos irregulares
- Peso: 30 kg
- Forma: Em forma de L
- Cor: cinzento
- Cabo de ligação à rede eléctrica: Euro, ficha (tipo C, CEE 7/16) - C7, tomada para aparelho, comprimento: 2 m

Attributes

- Color: Grey

Logistics

	Number (pcs)	Weight (kg)	Depth (cm)	Width (cm)	Height (cm)	cm³
Packaging Unit Carton	1	30.87	36.50	95.00	18.50	64,148.80
Packaging Unit Inside	1	30.87	36.50	95.00	18.50	64,148.80
Packaging Unit Single	1	30.87	36.50	95.00	18.50	64,148.80
Net single without Packaging	1	30.00	130.00	112.00	72.00	0.00

More images:



Safety notes

- This appliance can be used by children aged from 8 years and above and persons with reduced physical, sensory or mental capabilities or lack of experience and knowledge if they have been given supervision
- or instruction concerning use of the appliance in a safe way.
- device and understand the dangers involved
- Persons with reduced physical or mental capabilities or lack of experience and knowledge must not use the product unless they are supervised, understand the hazards involved or have been thoroughly instructed
- in the use of the appliance by a person responsible for their safety
- Children are not allowed to play with the device, as unforeseen actions while playing can lead to dangerous consequences for which the manufacturer is not responsible
- Familiarize yourself with all the functions and program settings of the appliance before using it for the first time.
- Carefully check the correct and complete assembly before use
- Cleaning and user maintenance must not be carried out by children without supervision
- If the mains cable is damaged, it must be replaced by the manufacturer, its customer service department or a similarly qualified person in order to avoid a hazard
- Make sure that there are no sources of danger in your working environment, e.g. do not throw the tools in the garbage.
- Always pay attention to the packaging materials to avoid possible dangers, e.g. plastic bags can lead to choking hazards for children.
- Keep the original packaging of the device, if necessary, in case you want to transport it later.
- Power supply: AC 100 V - 240 V, 50 / 60 Hz
- Operating temperature: 0 - 40°C
- Before cleaning, unplug the appliance, wipe the dust off the surface with a slightly damp tea towel, make sure that no drops get into the internal parts and

- do not lose the plug
- The electrical box contains electronic components, metals, plastics, wires, etc., so dispose of them in accordance with the environmental regulations of the respective country and not with general household waste.
- Slight noises caused by the V-ribbed belt or the brake system have no influence on the use of the appliance.
- Cleaning the appliance with corrosive or abrasive materials is prohibited. It must be ensured that the cleaning agent used does not pollute the environment.
- This appliance may only be used together with the power supply unit supplied. Any person responsible for installing or using the table in daily use or for servicing and repair work on this table should
- read these instructions carefully. Keep these instructions in the vicinity of your sitting/standing table.
- The table may only be used as a work table with the option of infinitely variable adjustment of the working height between a sitting and standing position. The table may only be used indoors and in dry rooms (office environment or similar).
- The table must not be overloaded - the maximum load is 120 kg. The motors may be operated continuously for a maximum of 2 minutes. After this, the motors must stand still for approx. 18 minutes before they can be used again.
- Failure to observe the safety and installation instructions in this manual may result in serious personal injury.
- Users should never sit on the work surface to avoid serious personal injury.
- Do not clean the appliance with water if it is still connected to the power supply.
- Do not disassemble or replace components while the appliance is connected to the mains supply
- Never operate the system with a damaged cable or plug.
- Never operate the system in a damp environment or if its electrical components come into contact with liquids.
- Do not operate the system if the control box causes noises or odors. Modifications to the appliance and the control box are not permitted.
- Remove all obstacles in the height adjustment area.
- To avoid tripping hazards, do not leave cables or plugs lying around disorderly.
- Any attempts to modify the table frame are not permitted
- Nothing may be attached to the adjustable connections of the table frame.
- Outdoor use is prohibited.
- When raising and lowering the table, maintain the required safety distance to avoid being trapped between the moving tabletop and fixed objects in the vicinity.
- When moving the table up and down, the user must ensure that nobody is injured and that no objects are damaged. The table top must not hit a solid object so that the table tips over. The office chair must be removed before the table is raised or lowered.
- Modifications to the switch box are strictly prohibited.
- The table must not be used as a lifting device for persons

EU responsible person

EU based economic operator ensuring the product complies with the required regulations.

ASSMANN Electronic GmbH
Auf dem Schüffel 3
Lüdenscheid, Germany
<https://www.assmann.com>
info@assmann.com