

DIGITUS Universal Dual Monitor Mount with Gas Spring and Clamp Mount

DA-90395

EAN 4016032465126



Dual Gas Spring Monitor Clamp Mount 15-32", 2x 9 kg (max.), black

With the universal dual monitor mount from DIGITUS®, you can conveniently attach two monitors with dimensions between 15" - 32" to your desk using a clamp mount. The quick release function also makes it easier for you to install the monitors. The VESA bracket is simply inserted into the corresponding mount and automatically snaps in. Without a great deal of effort, you can arrange the monitors according to your needs and pivot, incline or rotate the monitors, for instance for monitors in portrait mode. Support of the integrated gas spring facilitates height adjustment of your monitors. Do a good deed for yourself and your health by adjusting your monitor optimally for your body and your sitting position. The monitor cables can be stored in an orderly fashion using the cable routing included in delivery.

The dual monitor mount allows you to individually arrange two monitors from 15" - 32". The monitors can be swiveled, inclined and rotated - with integrated gas spring for easy height adjustment and quick release function.

- Suitable for monitors with dimensions between 15" and 32"
- Maximum load capacity: 9 kg per monitor arm

- Quick release function: Simple clipping in of the monitor in the mount
- Rotation of the VESA bracket: 180°
- Inclination of the VESA bracket: 180°
- Rotation of the VESA bracket: 180°
- Supports VESA dimensions: 75 x 75, 100 x 100
- Maximum height adjustment: 33.5 cm
- For tabletop thicknesses between: 10 - 85 mm
- Material: Aluminum, plastic, steel
- Dimensions: H 69 x W 104.8 x D 13.1 cm
- Weight of the bracket: 5.7 kg
- Color: Black, matte
- Monitor weight (max.): 9 kg
- Mounting method: Clamp-mount
- Number of monitors: 2
- Size of monitors: up to 32"
- VESA mount: 75x75 mm, 100x100 mm

Package contents

- Universal Dual Monitor Mount with Gas Spring and Clamp Mount
- Mounting accessories
- Installation instruction

Logistics						
	Number (pcs)	Weight (kg)	Depth (cm)	Width (cm)	Height (cm)	cm³
Packaging Unit Carton	2	14.60	36.50	46.00	36.00	60,444.00
Packaging Unit Inside	1	7.30	17.10	35.10	44.40	26,649.30
Packaging Unit Single	1	7.30	17.10	35.10	44.40	26,649.30
Net single without Packaging	1	5.75	13.10	104.80	69.00	0.00

The image is a 4x3 grid of 12 panels. The first three rows show the msa25 monitor arm in various configurations:

- Row 1: Two monitors in a horizontal split-screen setup on a desk.
- Row 2: Two monitors in a horizontal split-screen setup, viewed from a different angle.
- Row 3: A single monitor in a vertical orientation on a desk.
- Row 4: A single monitor in a vertical orientation, viewed from a different angle.
- Row 5: A single monitor in a horizontal orientation, viewed from a different angle.
- Row 6: A single monitor in a horizontal orientation, viewed from a different angle.
- Row 7: A single monitor in a horizontal orientation, viewed from a different angle.
- Row 8: A single monitor in a horizontal orientation, viewed from a different angle.
- Row 9: A single monitor in a horizontal orientation, viewed from a different angle.
- Row 10: A single monitor in a horizontal orientation, viewed from a different angle.
- Row 11: A single monitor in a horizontal orientation, viewed from a different angle.
- Row 12: A technical diagram of the msa25 monitor arm, showing its components and dimensions. The diagram includes labels for the msa25, msa25-1, msa25-2, msa25-3, msa25-4, msa25-5, msa25-6, msa25-7, msa25-8, msa25-9, msa25-10, msa25-11, msa25-12, msa25-13, msa25-14, msa25-15, msa25-16, msa25-17, msa25-18, msa25-19, msa25-20, msa25-21, msa25-22, msa25-23, msa25-24, msa25-25, msa25-26, msa25-27, msa25-28, msa25-29, msa25-30, msa25-31, msa25-32, msa25-33, msa25-34, msa25-35, msa25-36, msa25-37, msa25-38, msa25-39, msa25-40, msa25-41, msa25-42, msa25-43, msa25-44, msa25-45, msa25-46, msa25-47, msa25-48, msa25-49, msa25-50, msa25-51, msa25-52, msa25-53, msa25-54, msa25-55, msa25-56, msa25-57, msa25-58, msa25-59, msa25-60, msa25-61, msa25-62, msa25-63, msa25-64, msa25-65, msa25-66, msa25-67, msa25-68, msa25-69, msa25-70, msa25-71, msa25-72, msa25-73, msa25-74, msa25-75, msa25-76, msa25-77, msa25-78, msa25-79, msa25-80, msa25-81, msa25-82, msa25-83, msa25-84, msa25-85, msa25-86, msa25-87, msa25-88, msa25-89, msa25-90, msa25-91, msa25-92, msa25-93, msa25-94, msa25-95, msa25-96, msa25-97, msa25-98, msa25-99, msa25-100.